




CYBERSOLV® C8882

Understencil Wipe/Stencil Cleaning Solvent

CYBERSOLV® C8882 is a fast-acting stencil cleaning solvent designed for the understencil wipe and hand cleaning processes. Cybersolv C8882 instantly dissolves all flux types within the solder paste, including water soluble, rosin, and low residue no-clean fluxes.



- Removes All Flux Types
- Fast Drying
- Non-Flammable
- Does Not Interact or Remove Nano-Coatings
- Compatible to the Wetted Components of Automatic Stencil Printers

PRODUCT PROPERTIES	
pH (10g/L)	Not Applicable
FLASH POINT	142°F / 61°C
BOILING POINT	270°F / 132°C
WATER SOLUBLE	Partial
VOC, @ 100%	875.6 g/L

TYPICAL PROCESSES	
APPLICATION	Understencil, Hand-held Ultrasonic Cleaner & Manual
CONCENTRATION	100%
TEMPERATURE	Ambient
RINSE	No Rinse Required
DRY	None Required

The above process parameters are recommendations based on extensive testing done in KYZEN's Application Lab. Your KYZEN Sales Representative can assist you in optimizing your process parameters.

STORAGE AND HANDLING

- Packaged in Polyethylene Containers
- Store at 5-30°C/41-86°F in Original Container
- Standard Chemical Handling Practices
- Shelf Life of 5 Years, in Sealed Containers of 5 gallons / 25 liters or more

AVAILABILITY

- 1 Gallon
- 5 Liters*
- 5 Gallons
- 25 Liters*
- 55 Gallons
- 200 Liters*
- 16oz (500ml) Spray Bottles
- Presaturated Wipes
- * Liters Available in South Asia and Europe

CYBERSOLV® C8882

Understencil Wipe / Stencil Cleaning Solvent





ENVIRONMENTAL, HEALTH AND SAFETY REGULATIONS

CYBERSOLV® C8882 is a non-flammable, non-corrosive organic solvent solution. It contains no CFC's or HAP's. Refer to the Safety Data Sheet for more information.

REACH ✓ KYZEN is an ISO 9001:2008 company.



COMPATIBILITY

CYBERSOLV® C8882 is compatible with all materials commonly used in electronic assembly manufacturing and cleaning processes. For specific compatibility information, please contact your KYZEN representative.



FREE CLEANING TRIALS AND PROCESS OPTIMIZATIONS

KYZEN will conduct complimentary trials at your factory or "risk-free" testing in one of our global Applications Laboratories in North America, Asia or Europe to ensure you achieve your goal. Increase your yields and product reliability by identifying and tuning the critical parameters of your cleaning process. With our commitment to science and understanding process, KYZEN has the flexibility to simulate and refine any cleaning process – including yours!

Each laboratory is fully equipped with an extensive array of cleaning and analytical equipment, including, but not limited to:

- Batch Washers
- In-Line Washers
- SUI Systems
- Vapor Degreasers
- GC (TCD and FID)
- Scanning Electron Microscope (SEM)
- Ultrasonic Systems
 Ion Chromatography
 - FTIR Spectrophotometer
 - Humidity Chamber
 - High Powered Microscopes





Aqueous, Semi-Aqueous and Vapor Phase Chemistries • Process Evaluation and Optimization **Contract Cleaning • Cleanliness Testing • Soil Analysis**

KYZEN.com

Penang, Malaysia SOUTHEAST ASIAN HEADQUARTERS +60 4 630 3000

Maldegem, Belgium **EUROPEAN HEADQUARTERS** +32 50 395 374

Nashville, TN GLOBAL HEADQUARTERS (615) 831-0888

Manchester, NH NORTH AMERICAN OPERATIONS FACILITY (603) 622-2900

The information contained herein is based on available data from reliable sources and is accurate to the best of KYZEN Corporation's knowledge at the time of this publication. The user is solely responsible for determining the suitability and completeness of such information for their particular application and for adopting appropriate safety precautions. This data is not to be taken as a warranty or representation for which KYZEN assumes legal or financial responsibility. 062515